



# SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 01/27/2015

Version 1.1

## SECTION 1. Identification

### Product identifier

Product number	PX2014
Product name	Pyridine For HPLC and Spectrophotometry OmniSolv®
CAS-No.	110-86-1

### Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis
-----------------	----------------------

### Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation   290 Concord Road, Billerica, MA 01821, United States of America   General Inquiries: +1-978-715-4321   Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

## SECTION 2. Hazards identification

### GHS Classification

Flammable liquid, Category 2, H225  
Acute toxicity, Category 4, Oral, H302  
Acute toxicity, Category 4, Inhalation, H332  
Acute toxicity, Category 4, Dermal, H312  
For the full text of the H-Statements mentioned in this Section, see Section 16.

### GHS-Labeling

#### Hazard pictograms



Signal Word  
Danger

#### Hazard Statements

H225 Highly flammable liquid and vapor.  
H302 + H312 + H332 Harmful if swallowed, in contact with skin or if inhaled.

# SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

PX2014

Version 1.1

Product name

Pyridine For HPLC and Spectrophotometry OmniSolv®

---

## *Precautionary Statements*

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P233 Keep container tightly closed.

P240 Ground/bond container and receiving equipment.

P241 Use explosion-proof electrical/ ventilating/ lighting/ equipment.

P242 Use only non-sparking tools.

P243 Take precautionary measures against static discharge.

P261 Avoid breathing dust/ fume/ gas/ mist/ vapors/ spray.

P264 Wash skin thoroughly after handling.

P270 Do not eat, drink or smoke when using this product.

P271 Use only outdoors or in a well-ventilated area.

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

P301 + P312 IF SWALLOWED: Call a POISON CENTER or doctor/ physician if you feel unwell.

P303 + P361 + P353 IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower.

P304 + P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

P312 Call a POISON CENTER or doctor/ physician if you feel unwell.

P322 Specific measures (see supplemental first aid instructions on this label).

P330 Rinse mouth.

P363 Wash contaminated clothing before reuse.

P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam for extinction.

P403 + P235 Store in a well-ventilated place. Keep cool.

P501 Dispose of contents/ container to an approved waste disposal plant.

## **Other hazards**

None known.

---

## **SECTION 3. Composition/information on ingredients**

Formula C5H5N (Hill)

Molar mass 79.1 g/mol

### **Hazardous ingredients**

*Chemical Name (Concentration)*

CAS-No.

*Pyridine (>= 90 % - <= 100 % )*

110-86-1

Exact percentages are being withheld as a trade secret.

---

## **SECTION 4. First aid measures**

### **Description of first-aid measures**

#### *Inhalation*

After inhalation: fresh air. If breathing stops: mouth-to-mouth breathing or artificial respiration.

Oxygen if necessary. Immediately call in physician.

#### *Skin contact*

After skin contact: wash off with plenty of water. Remove contaminated clothing. Consult a physician.

---

# SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

PX2014

Version 1.1

Product name

Pyridine For HPLC and Spectrophotometry OmniSolv®

---

### *Eye contact*

After eye contact: rinse out with plenty of water.

### *Ingestion*

After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

### **Most important symptoms and effects, both acute and delayed**

irritant effects, Cough, Shortness of breath, narcosis, Nausea, Vomiting, cardiovascular disorders, collapse, Headache, insomnia, restlessness

### **Indication of any immediate medical attention and special treatment needed**

No information available.

---

## **SECTION 5. Fire-fighting measures**

### **Extinguishing media**

#### *Suitable extinguishing media*

Carbon dioxide (CO<sub>2</sub>), Foam, Dry powder, Water

#### *Unsuitable extinguishing media*

For this substance/mixture no limitations of extinguishing agents are given.

### **Special hazards arising from the substance or mixture**

Combustible.

Vapors are heavier than air and may spread along floors.

Forms explosive mixtures with air at ambient temperatures.

Pay attention to flashback.

Development of hazardous combustion gases or vapors possible in the event of fire.

Fire may cause evolution of:

nitrogen oxides

### **Advice for firefighters**

#### *Special protective equipment for fire-fighters*

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

#### *Further information*

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system. Remove container from danger zone and cool with water.

---

## **SECTION 6. Accidental release measures**

### **Personal precautions, protective equipment and emergency procedures**

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact.

Ensure adequate ventilation. Keep away from heat and sources of ignition. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

### **Environmental precautions**

---

# SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

PX2014

Version 1.1

Product name

Pyridine For HPLC and Spectrophotometry OmniSolv®

Do not empty into drains. Risk of explosion.

## Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent and neutralizing material (e.g. Chemizorb® OH<sup>-</sup>, Art. No. 101596).

Dispose of properly. Clean up affected area.

---

## SECTION 7. Handling and storage

### Precautions for safe handling

Observe label precautions.

Work under hood. Do not inhale substance/mixture. Avoid generation of vapors/aerosols.

### *Advice on protection against fire and explosion*

Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharge.

### Conditions for safe storage, including any incompatibilities

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat and sources of ignition.

Store at room temperature.

---

## SECTION 8. Exposure controls/personal protection

### Exposure limit(s)

#### *Ingredients*

Basis	Value	Threshold limits	Remarks
<i>Pyridine 110-86-1</i>			
ACGIH	Time Weighted Average (TWA):	1 ppm	
NIOSH/GUIDE	Recommended exposure limit (REL):	5 ppm 15 mg/m <sup>3</sup>	
OSHA_TRANS	PEL:	5 ppm 15 mg/m <sup>3</sup>	
Z1A	Time Weighted Average (TWA):	5 ppm 15 mg/m <sup>3</sup>	

### Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

### Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

### *Hygiene measures*

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

# SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

PX2014

Version 1.1

Product name

Pyridine For HPLC and Spectrophotometry OmniSolv®

---

### *Eye/face protection*

Safety glasses

### *Hand protection*

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

### *Other protective equipment:*

Flame retardant antistatic protective clothing.

### *Respiratory protection*

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

---

## SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	characteristic
Odor Threshold	0.0001 - 20.1 ppm
pH	ca. 8.5 at 16 g/l 68 °F (20 °C)
Melting point	-42 °C
Boiling point/boiling range	ca. 239 °F (115 °C) at 1,013 hPa
Flash point	63 °F (17 °C) Method: c.c.
Evaporation rate	12.7
Flammability (solid, gas)	No information available.
Lower explosion limit	1.7 %(V)
Upper explosion limit	10.6 %(V)
Vapor pressure	20 hPa at 68 °F (20 °C)
Relative vapor density	2.73

# SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

PX2014

Version 1.1

Product name

Pyridine For HPLC and Spectrophotometry OmniSolv®

---

Density	0.982 g/cm <sup>3</sup> at 68 °F (20 °C)
Relative density	No information available.
Water solubility	at 68 °F (20 °C) soluble
Partition coefficient: n-octanol/water	log Pow: 0.65 (experimental) (Lit.) Bioaccumulation is not expected.
Autoignition temperature	No information available.
Decomposition temperature	ca.914 °F (490 °C)
Viscosity, dynamic	0.95 mPa.s at 68 °F (20 °C)
Explosive properties	Not classified as explosive.
Oxidizing properties	none
Ignition temperature	900 °F (482 °C)

---

## SECTION 10. Stability and reactivity

### Reactivity

Vapors may form explosive mixture with air.

### Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

### Possibility of hazardous reactions

Violent reactions possible with:

Oxidizing agents, Acid anhydrides, acid halides

Exothermic reaction with:

Risk of ignition or formation of inflammable gases or vapors with:

Fluorine, halogen-halogen compounds, chlorosulfonic acid, chromium(VI) oxide, fuming sulfuric acid, perchromates, Nitric acid, sulfuric acid, silver salt, perchlorates, nitrogen dioxide

Risk of explosion with:

perchloric acid, nitrogen oxides

### Conditions to avoid

Warming.

### Incompatible materials

rubber, various plastics, various metals

# SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

PX2014

Version 1.1

Product name

Pyridine For HPLC and Spectrophotometry OmniSolv®

---

## Hazardous decomposition products

in the event of fire: See section 5.

---

## SECTION 11. Toxicological information

### Information on toxicological effects

#### *Likely route of exposure*

Inhalation, Eye contact, Skin contact

#### *Target Organs*

Eyes

Skin

Central nervous system

Liver

Kidneys

gastrointestinal tract

#### *Acute oral toxicity*

LD50 Rat: 891 mg/kg (RTECS)

absorption

Symptoms: Vomiting, Nausea

#### *Acute inhalation toxicity*

LC50 Rat: 17.75 mg/l; 4 h

US-EPA

absorption

Symptoms: mucosal irritations, Cough, Shortness of breath

#### *Acute dermal toxicity*

LD50 Rabbit: 1,121 mg/kg

(RTECS)

absorption

#### *Skin irritation*

Rabbit

Result: slight irritation

(RTECS)

#### *Eye irritation*

Rabbit

Result: Severe irritations

(Lit.)

#### *Sensitization*

Sensitization test: Guinea pig

Result: negative

(Lit.)

#### *Genotoxicity in vivo*

Micronucleus test

Result: negative

(National Toxicology Program)

# SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

PX2014

Version 1.1

Product name

Pyridine For HPLC and Spectrophotometry OmniSolv®

---

Chromosome aberration test

Result: negative

(National Toxicology Program)

*Genotoxicity in vitro*

Ames test

Result: negative

(Lit.)

*Teratogenicity*

Did not show teratogenic effects in animal experiments. (External MSDS)

*Specific target organ systemic toxicity - single exposure*

The substance or mixture is not classified as specific target organ toxicant, single exposure.

*Specific target organ systemic toxicity - repeated exposure*

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

*Aspiration hazard*

Regarding the available data the classification criteria are not fulfilled.

## Carcinogenicity

IARC

No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

OSHA

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

ACGIH

Confirmed animal carcinogen with unknown relevance to humans.

Pyridine

110-86-1

## Further information

Systemic effects:

After uptake:

Headache, restlessness, insomnia

In high doses:

narcosis, cardiovascular disorders, Circulatory collapse

Chronic uptake results in damage of:

Liver, Kidney

Good warning effect due to low odor threshold.

Handle in accordance with good industrial hygiene and safety practice.

---

## SECTION 12. Ecological information

### Ecotoxicity

*Toxicity to fish*

LC50 *Oncorhynchus mykiss* (rainbow trout): 4.6 mg/l; 96 h (ECOTOX Database)

---

# SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

PX2014

Version 1.1

Product name

Pyridine For HPLC and Spectrophotometry OmniSolv®

---

### *Toxicity to daphnia and other aquatic invertebrates*

EC5 E.sulcatum: 3.5 mg/l; 72 h (Lit.) (maximum permissible toxic concentration)

EC50 Daphnia magna (Water flea): 240 mg/l; 24 h (ECOTOX Database)

### *Toxicity to algae*

IC5 Scenedesmus quadricauda (Green algae): 120 mg/l; 7 d (Lit.) (maximum permissible toxic concentration)

### *Toxicity to bacteria*

EC5 Pseudomonas putida: 340 mg/l; 16 h (Lit.) (maximum permissible toxic concentration)

## **Persistence and degradability**

No information available.

## **Bioaccumulative potential**

*Partition coefficient: n-octanol/water*

log Pow: 0.65

(experimental)

(Lit.) Bioaccumulation is not expected.

## **Mobility in soil**

No information available.

### *Additional ecological information*

Forms toxic mixtures in water, dilution measures notwithstanding.

Discharge into the environment must be avoided.

---

## **SECTION 13. Disposal considerations**

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

---

## **SECTION 14. Transport information**

### **Land transport (DOT)**

UN number	UN 1282
Proper shipping name	PYRIDINE
Class	3
Packing group	II
Environmentally hazardous	--

### **Air transport (IATA)**

UN number	UN 1282
Proper shipping name	PYRIDINE
Class	3
Packing group	II
Environmentally hazardous	--
Special precautions for user	no

### **Sea transport (IMDG)**

---

**SAFETY DATA SHEET**

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

PX2014

Version 1.1

Product name

Pyridine For HPLC and Spectrophotometry OmniSolv®

---

**UN number** UN 1282  
**Proper shipping name** PYRIDINE  
**Class** 3  
**Packing group** II  
**Environmentally hazardous** --  
**Special precautions for user** yes  
**EmS** F-E S-D

---

**SECTION 15. Regulatory information**

**United States of America**

**SARA 313**

The following components are subject to reporting levels established by SARA Title III, Section 313:

*Ingredients*

Pyridine	110-86-1	100 %
----------	----------	-------

**SARA 302**

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

**Clean Water Act**

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

**DEA List I**

Not listed

**DEA List II**

Not listed

**US State Regulations**

**Massachusetts Right To Know**

*Ingredients*

Pyridine

**Pennsylvania Right To Know**

*Ingredients*

Pyridine

**New Jersey Right To Know**

*Ingredients*

Pyridine

**California Prop 65 Components**

WARNING: this product contains a chemical known in the State of California to cause cancer.

*Ingredients*

Pyridine

---

# SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number  
Product name

PX2014  
Pyridine For HPLC and Spectrophotometry OmniSolv®

Version 1.1

## Notification status

TSCA: All components of the product are listed in the TSCA-inventory.  
DSL: All components of this product are on the Canadian DSL.  
KOREA: Not in compliance with the inventory

## SECTION 16. Other information

### Training advice

Provide adequate information, instruction and training for operators.

### Labeling

*Hazard pictograms*



### *Signal Word*

Danger

### *Hazard Statements*

H225 Highly flammable liquid and vapor.  
H302 + H312 + H332 Harmful if swallowed, in contact with skin or if inhaled.

### *Precautionary Statements*

Prevention  
P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.  
P240 Ground/bond container and receiving equipment.  
Response  
P302 + P352 IF ON SKIN: Wash with plenty of soap and water.  
Storage  
P403 + P233 Store in a well-ventilated place. Keep container tightly closed.

### Full text of H-Statements referred to under sections 2 and 3.

H225 Highly flammable liquid and vapor.  
H302 Harmful if swallowed.  
H312 Harmful in contact with skin.  
H332 Harmful if inhaled.

### Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at [www.wikipedia.org](http://www.wikipedia.org).

# SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

PX2014

Version 1.1

Product name

Pyridine For HPLC and Spectrophotometry OmniSolv®

---

Revision Date 01/27/2015

---

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

*All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.*